


## ANSI Hochtemperatur-Glasfaser-Thermoelemente mit zwei verdrehten, freiliegenden, geschweiften Spitzen und Standard-Steckeranschluss



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockings of Thermocouple Cables. The Company has been trading since 1971 and is ISO9001 accredited.

### Mssen Sie Ihren Temperatursensor kalibrieren?

Labfacility ist auf ISO17025 (UKAS)-Kalibrierstandards rckfhrbar und bietet die Wahl zwischen einer 3- oder 5-Punkt-rckfhrbaren Kalibrierung mit unserer hauseigenen Kalibriereinrichtung.

**Bitte beachten Sie, dass Sie bezglich der Lieferinformationen kontaktiert werden, wenn Sie Ihrer Bestellung eine Kalibrierungsoption hinzufügen.**

### Leistungsbeschreibung

## Specifications

<b>General Description</b>	Fast response, welded exposed junction. Good temperature resistance (not suitable in fluids).
<b>Thermocouple Type</b>	K
<b>Thermocouple Junction</b>	Exposed
<b>Cable Length</b>	5, 10 or 20-metre-long
<b>Cable Type</b>	high temperature glassfibre insulated twisted cable
<b>Core / Strands</b>	1/0.711mm conductors (21awg)
<b>Cable Termination</b>	Standard plug termination
<b>Max. Temperature</b>	+700°C
<b>Min. Temperature</b>	0°C
<b>Tolerance</b>	Tolerance to ANSI MC96.1 Class 2
<b>Standards Met</b>	Colour code to ANSI MC96.1