


Typ J Glasfaser isoliert Flachpaar Kabel / Draht mit Edelstahl Overbraid (BS)

TYpe J, 14/0.2mm
SSOB PTFE



Typ J Glasfaser isoliert Flachpaar Kabel / Draht mit Edelstahl Overbraid (BS)

Bild ist nur für Farbcodierung summieren

Der Preis ist pro Meter - bitte fügen Sie die erforderliche Menge für den Korb. Nur noch 336 Meter auf Lager

Glasfaser isolierte Flachpaarkonstruktion, Leiter flach gelegt, Glasfaser isoliert mit Glasfasermantel, Silikon lackiert durch und durch + Edelstahl-Overbraid für zusätzlichen Schutz und mechanische Festigkeit. Gute Temperaturbeständigkeit, aber nicht geeignet, wo Flüssigkeiten vorhanden sind.

Spezifikationen
Specifications

| | |
|----------------------------|---|
| Product Code | WJ-247-D |
| General Description | Good temperature range but will not prevent ingress of fluids. Fairly flexible but does not provide good mechanical protection. |
| Cable Length | Priced per metre |
| Cable Type | SSOB PTFE |
| Core / Strands | 14/0.2mm |
| Outer Colour | Black |
| + Colour | Yellow |
| - Colour | Blue |
| Insulation Material | Glassfibre insulated extension cable with stainless steel overbraiding |
| Max. Temperature | +350°C (short periods up to 400°C) |
| Min. Temperature | -60°C |
| + Conductor | Iron |
| - Conductor | Constantan |



LABFACILITY

TEMPERATURE & PROCESS TECHNOLOGY

| | |
|-------------------|---------|
| Standards Met | BS |
| Thermocouple Type | J |
| Tolerance | Class 2 |