


Typ J Glasfaser isoliert Flachpaar Kabel / Draht mit Edelstahl Overbraid (BS)

TYpe J, 14/0.2mm
SSOB PTFE



Typ J Glasfaser isoliert Flachpaar Kabel / Draht mit Edelstahl Overbraid (BS)

Bild ist nur für Farbcodierung summieren

Der Preis ist pro Meter - bitte fügen Sie die erforderliche Menge für den Korb. Nur noch 336 Meter auf Lager

Glasfaser isolierte Flachpaarkonstruktion, Leiter flach gelegt, Glasfaser isoliert mit Glasfasermantel, Silikon lackiert durch und durch + Edelstahl-Overbraid für zusätzlichen Schutz und mechanische Festigkeit. Gute Temperaturbeständigkeit, aber nicht geeignet, wo Flüssigkeiten vorhanden sind.

Spezifikationen
Specifications

Product Code	WJ-247-D
General Description	Good temperature range but will not prevent ingress of fluids. Fairly flexible but does not provide good mechanical protection.
Cable Length	Priced per metre
Cable Type	SSOB PTFE
Core / Strands	14/0.2mm
Outer Colour	Black
+ Colour	Yellow
- Colour	Blue
Insulation Material	Glassfibre insulated extension cable with stainless steel overbraiding
Max. Temperature	+350°C (short periods up to 400°C)
Min. Temperature	-60°C
+ Conductor	Iron
- Conductor	Constantan



LABFACILITY

TEMPERATURE & PROCESS TECHNOLOGY

Standards Met	BS
Thermocouple Type	J
Tolerance	Class 2