


## Typ J Glasfaser isoliert Flachpaar Kabel / Draht mit Edelstahl Overbraid (BS)

TYpe J, 14/0.2mm  
SSOB PTFE



**Typ J Glasfaser isoliert Flachpaar Kabel / Draht mit Edelstahl Overbraid (BS)**

Bild ist nur für Farbcodierung summieren

**Der Preis ist pro Meter - bitte fügen Sie die erforderliche Menge für den Korb. Nur noch 336 Meter auf Lager**

Glasfaser isolierte Flachpaarkonstruktion, Leiter flach gelegt, Glasfaser isoliert mit Glasfasermantel, Silikon lackiert durch und durch + Edelstahl-Overbraid für zusätzlichen Schutz und mechanische Festigkeit. Gute Temperaturbeständigkeit, aber nicht geeignet, wo Flüssigkeiten vorhanden sind.

**Spezifikationen**
**Specifications**

<b>Product Code</b>	WJ-247-D
<b>General Description</b>	Good temperature range but will not prevent ingress of fluids. Fairly flexible but does not provide good mechanical protection.
<b>Cable Length</b>	Priced per metre
<b>Cable Type</b>	SSOB PTFE
<b>Core / Strands</b>	14/0.2mm
<b>Outer Colour</b>	Black
<b>+ Colour</b>	Yellow
<b>- Colour</b>	Blue
<b>Insulation Material</b>	Glassfibre insulated extension cable with stainless steel overbraiding
<b>Max. Temperature</b>	+350°C (short periods up to 400°C)
<b>Min. Temperature</b>	-60°C
<b>+ Conductor</b>	Iron
<b>- Conductor</b>	Constantan



# LABFACILITY

TEMPERATURE & PROCESS TECHNOLOGY

Standards Met	BS
Thermocouple Type	J
Tolerance	Class 2