

Hermetisch abgedichteter Draht-Thermistor-Sensor



[Click here to view product](#)

Product Code	XE-9874
General Description	An IP67 sensor that is hermetically sealed for use in corrosive or wet environments
Sensor Type	Hermetically sealed thermistor
Thermistor	10K NTC Thermistor
BETA 25/85	3977K
Cable Length	1, 2 & 5m
Cable Type	2 wire flexible 7/0.2mm stranded conductors (24AWG) with 75mm tails
Core / Strands	7/0.2mm (24AWG)
Cable Termination	75mm Bare Tails
Max. Temperature	+150Å°C

Min. Temperature	-30Â°C
IP Rating	67
Accuracy	+/- 0.2K (over 0-70Â°C)
Important Information	Pressure tested at 40 PSI as standard