


Oberflächenmontierbarer RTD-Sensor



[Click here to view product](#)

Product Code	XE-7700
General Description	Stripped 75mm tails as standard
Sensor Type	Pt100
Fitting	3mm mounting hole
Cable Type	PFA
Termination Type	Bare Tails or Miniature 3-Pin Plug Options
Max. Temperature	230Â°C
Min. Temperature	-50Â°C
Tolerance	Class A
Length	1M, 2M or 5M Lead

Number of Wires	4 wire or 3 wire with connector
------------------------	---------------------------------

